



premium5

The premium5 shares the same overlay specifications as its premium5digital cousin but makes use of the analogue control unit.

As with the premium5digital, the premium5 has sealed infection controlled seams and spring loaded air hoses to prevent kinking. Heavy duty securing straps effectively bond the overlay to any single mattress.**

Use only with the consent and supervision of a suitably qualified health professional.

** Mattress not included.

product specification

The whole system is completely modular allowing easy component replacement.

Micro air loss cells in the centre section assist in keeping the system and user moisture free.

Quick Facts

- Mattress overlay system
- Care level - Medium Risk
- 1 in 2 alternation with static head section
- Analogue control unit with adjustable static settings
- Heavy duty securing straps
- Micro air loss cells
- Spring loaded anti kink air hoses

control unit

control interface	analogue
dimensions (WxHxD mm)	290x272x128mm
weight	2.9kg
air output	6.5 litres per minute
hose connection type	quick release connectors
timed static function	x
alarms	visual
internal power down alarm	x
fuse rating (Amps)	mains plug - 3A, control unit 1A (x2)
mode of operation	continuous
electrical safety	EN 60601.1:1996, UL2601-1 safe

support surface

support type	mattress overlay
dimensions (LxWxH millimetres)	2000x880x175mm
alternation type	1 in 2
alternation cycle time	12 minutes
base material	TPU coated nylon 420 denier woven fabric
cell material	TPU coated 210 denier nylon fabric
cell in cell technology	x
side buffer	✓ (optional)
number of cells	18
static head cells	✓
CPR function	pull tag
anti kink hosing	✓
micro air loss feature	✓
positioning handles	✓

top cover

top cover material	PU coated 2 way stretch nylon
attachment type	quick release zipper
Infection control side skirts	✓
seam joining	tape sealed

general

risk category	medium risk
maximum user weight guide	150kg
carry bag included	✓